

5-557972-3

Modular Plug, 8P/8C, unshielded, flat oval, small conductor, 8-position, category 5, 100 pcs

OBSOLETE

This product was discontinued on: August 14, 2018

Replaced By:

6-557972-3 MP-88U-FS-1	Modular Plug, 8P/8C, unshielded, small conductor, flat oval, 2.54 x 8.89 mm max cable jack OD, 100 /bag
---------------------------	---

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	5
Cable Type	Flat oval, unshielded
Conductor Type	Solid
Interface	RJ45
Positions/Loaded Contacts	8/8
Termination Type	IDC

Electrical Specifications

Current Rating, maximum	0.75 A
Insulation Resistance, minimum	500 mOhm
Safety Voltage Rating	150 Vac

Material Specifications

Contact Base Material	Phosphor Bronze
Material Type	Glass filled polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	750 times
------------------------------	-----------

5-557972-3

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing
Flammability Rating	UL 94 V-2

Packaging and Weights

Packaging quantity	100
Packaging Type	Bag Box Carton