

5-569452-2

Modular Plug, 4P/4C, unshielded, round, 4-position, category 3, 500 pcs

OBSOLETE
This product was discontinued on: August 14, 2018
Replaced By:
6-569031-2
MP-44U-R-5

Modular Plug, 4P/4C, unshielded, headset, round, 2.8 mm max cable jack OD, category 3, 4-position, 500/bag

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	3
Cable Type	Round, unshielded
Conductor Type	Solid
Interface	RJ9
Positions/Loaded Contacts	4/4
Termination Type	IDC

Electrical Specifications

Insulation Resistance, minimum	500 mOhm
--------------------------------	----------

Material Specifications

Contact Base Material	Phosphor Bronze
Material Type	Glass filled polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	750 times
------------------------------	-----------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
-----------------------	--------------------------------------

5-569452-2

Flammability Rating	UL 94 V-2
Packaging and Weights	
Packaging quantity	500
Packaging Type	Bag Box Carton