

5-641335-3

Modular Plug Assembly, RJ11, category 3, 4-position, standard latch

OBSOLETE

This product was discontinued on: April 1, 2016

Replaced By:

6-641335-3 MP-64U-F-1	Modular Plug, 6P/4C, unshielded, flat oval, 0.86 – 0.99 mm insulation OD, 6-position, category 3, 100 /bag
--------------------------	--

Product Classification

Regional Availability	North America
Portfolio	NETCONNECT®
Product Type	Modular plug

General Specifications

ANSI/TIA Category	3
Cable Type	Round, unshielded
Conductor Type	Stranded
Interface	RJ11
Positions/Loaded Contacts	6/4
Termination Type	IDC

Dimensions

Compatible Cable Diameter, maximum	4.83 mm 0.19 in
Compatible Cable Diameter, minimum	2.29 mm 0.09 in

Electrical Specifications

Current Rating, maximum	0.75 A
Insulation Resistance, minimum	500 mOhm
Safety Voltage Rating	150 Vac

Material Specifications

Contact Base Material	Phosphor Bronze
Material Type	Glass filled polycarbonate

5-641335-3

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Relative Humidity Up to 93%, non-condensing

Flammability Rating UL 94 V-2

Packaging and Weights

Packaging quantity 100

Packaging Type Bag | Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

