



Modular Plug Kit, category 6A, shielded, 8-position, 5.7 – 7.0 mm max cable jack OD, 100/bag

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

Modular plug

General Specifications

ANSI/TIA Category

6A

Cable Type

Round, shielded

Conductor Type

Solid | Stranded

Interface

RJ45

Positions/Loaded Contacts

8/8

Termination Type

IDC

Dimensions

Compatible Cable Diameter, maximum

7 mm | 0.276 in

Compatible Cable Diameter, minimum

5.7 mm | 0.224 in

Compatible Insulated Conductor Diameter, maximum

1.09 mm | 0.043 in

Compatible Insulated Conductor Diameter, minimum

0.89 mm | 0.035 in

Contact Plating Thickness

1.27 µm

Compatible Conductor Gauge, solid

26–23 AWG

Compatible Conductor Gauge, stranded

26–23 AWG

Electrical Specifications

Insulation Resistance, minimum

500 mOhm

Material Specifications

Contact Base Material	Phosphor bronze
Contact Plating Material	Gold
Material Type	Glass filled polycarbonate
Plug Shield Base Material	Stainless steel
Plug Shield Plating Material	Nickel

Mechanical Specifications

Plug Insertion Life, minimum	750 times
-------------------------------------	-----------

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	UL 1863

Packaging and Weights

Packaging quantity	100
Packaging Type	Bag Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

