



Highway Media Outlet, 8-position, 4-contact, bag of 10, gray

Product Classification

Regional Availability	Australia/New Zealand
Product Type	Modular jack

General Specifications

ANSI/TIA Category	3
Cable Type	Unshielded
Color	Gray
Conductor Type	Solid Stranded
Integrated Dust Cover Type	None
Outlet Type	Standard
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class C
Wiring	T568A T568B

Dimensions

Panel Thickness, recommended	1.6 mm 0.063 in
-------------------------------------	-------------------

Electrical Specifications

PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles
-----------------------	--

Material Specifications

Material Type	Polycarbonate
----------------------	---------------

Mechanical Specifications

Plug to Jack Mating Cycles	Complies to IEC 60603-7 series
-----------------------------------	--------------------------------

64671105-00 | 64671105-00

Environmental Specifications

Flammability Rating

UL 94 V-0

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

