



FMK Series Modular Jack, 8-position, RJ45, category 5e, T568A/B, bag of 10, blue

- High speed data and voice transmission outlets
- Suitable for direct termination of 100Ω twisted pair insulated copper wires
- Compatible with the LSA-PLUS® insertion tool and 110 punchdown tool

OBSOLETE

This product was discontinued on: December 22, 2019

Product Classification

Regional Availability	Australia/New Zealand
Product Type	Modular jack
Product Series	FMK

General Specifications

ANSI/TIA Category	5e
Cable Type	Unshielded
Color	Blue
Conductor Type	Solid Stranded
Integrated Dust Cover Type	None
Outlet Type	Standard
Termination Punchdowns, minimum	200 times
Termination Tool	LSA-PLUS Punchdown tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class D
Wiring	T568A T568B

Dimensions

Panel Thickness, recommended	1.6 mm 0.063 in
Compatible Conductor Gauge, solid	24–22 AWG

64674072-40 | 6467 4 072-40

Compatible Conductor Gauge, stranded

26-24 AWG

Material Specifications

Material Type

Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum

2500 times

Environmental Specifications

Operating Temperature

-20 °C to +70 °C (-4 °F to +158 °F)

Storage Temperature

-20 °C to +70 °C (-4 °F to +158 °F)

Relative Humidity

Up to 93%, non-condensing

Flammability Rating

UL 94 V-0

Packaging and Weights

Packaging quantity

10

Packaging Type

Bag