

OCC1A Wideband Splitter, singlemode, 1x2, 60/40 ratio, 0.250 mm cable, light duty housing



## Product Classification

|                              |                    |
|------------------------------|--------------------|
| <b>Regional Availability</b> | North America      |
| <b>Product Type</b>          | Splitter component |
| <b>Product Series</b>        | OCC1A              |

## General Specifications

|                           |                          |
|---------------------------|--------------------------|
| <b>Device Type</b>        | Component, tubular       |
| <b>Functionality</b>      | Splitting                |
| <b>Technology Type</b>    | Fused biconic tapered    |
| <b>Application</b>        | For use in FOSS closures |
| <b>Circuits, quantity</b> | 1                        |
| <b>Distribution Type</b>  | 1 x 2 splitter           |
| <b>Interface, Input</b>   | Stub tail                |
| <b>Interface, Output</b>  | Stub tail                |
| <b>Split Ratio</b>        | 60/40                    |
| <b>Splitter, quantity</b> | 1                        |

## Dimensions

|                                 |                   |
|---------------------------------|-------------------|
| <b>Pigtail Length, Input</b>    | 2.5 m   8.202 ft  |
| <b>Pigtail Length, Output</b>   | 2.5 m   8.202 ft  |
| <b>Pigtail Diameter, Input</b>  | 0.25 mm   0.01 in |
| <b>Pigtail Diameter, Output</b> | 0.25 mm   0.01 in |

## Packaging and Weights

460159106 | OCC1A-1240-NNANQNA-TAP

---

**Packaging quantity** 1