

860634939 | OCC1P-23200-L2SESEB



OCC1P Wideband Splitter, planar, singlemode, 2x32, symmetrical split ratio, LC/APC, 0.9 mm cable, medium duty housing

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Splitter component
Product Series	OCC1P

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	2 x 32 splitter
Interface, Input	LC/APC
Interface, Output	LC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Pigtail Length, Input	1.5 m 4.921 ft
Pigtail Length, Output	1.5 m 4.921 ft
Pigtail Diameter, Input	0.9 mm 0.035 in
Pigtail Diameter, Output	0.9 mm 0.035 in

Environmental Specifications

Qualification Standards	Telcordia GR-1209-CORE Telcordia GR-1221-CORE
--------------------------------	---

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

