



## OCAB Outdoor fiber distribution cabinet

- OCAB is an all-purpose metal outdoor cabinet optimized solution to accommodate the 19 inch FACT and MFPS shelf product families
- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Serves as a cross-connect or interconnect cabinet with any combination of spliced and connectorized splitters
- A swing handle with half cylinder lock and 3 point latch system prevents unauthorized access
- The standard included base allows easy entry, fixation, identification and sealing of the cables
- Usable 19-inch panel-height is 18 RU
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber cross-connect hub
<b>Product Series</b>	OCAB

## General Specifications

<b>Access</b>	Front   Single door
<b>Color</b>	Green
<b>Lock Type</b>	Swivel with half cylinder lock (EURO DIN)
<b>Mounting</b>	In-ground root   Partially buried   Pre-fabricated base

## Dimensions

<b>Height</b>	1301 mm   51.221 in
<b>Width</b>	800 mm   31.496 in
<b>Depth</b>	320 mm   12.598 in
<b>Enclosure Size</b>	Medium

## Material Specifications

<b>Finish</b>	Powder coated polyester
---------------	-------------------------

# 760248006 | OCAB-P-S1-02

---

**Material Type** Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

## Environmental Specifications

**Environmental Space** Above ground

**Qualification Standards** IEC 60529, IP55 | IK10

## Packaging and Weights

**Included** Base with covers | Blank cable inlet plate | Cable inlet plate with 6 PG21 blind plugs | Mounting profiles for shelves

**Packaging quantity** 2

**Packaging Type** Pallet

**Note** Two cabinets supplied per Euro pallet, bolted and shrink wrapped in polythene with cardboard hosing protection strapped together for secure shipping