



OCAB Outdoor fiber distribution cabinet

- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Serves as a cross-connect or interconnect cabinet with any combination of spliced and connectorized splitters
- A swing handle with half cylinder lock and 3 point latch system prevents unauthorized access
- The standard included base allows easy entry, fixation, identification and sealing of the cables
- Usable 19-inch panel-height is 18 RU + 18 RU with 6 RU + 6 RU for the cable termination plate
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

Product Classification

Regional Availability	EMEA
Product Type	Fiber cross-connect hub
Product Series	OCAB

General Specifications

Access	Double door Front
Color	Light Gray (RAL 7035)
Lock Type	Swivel with half cylinder lock (EURO DIN)
Mounting	In-ground root Pre-fabricated base

Dimensions

Height	1553 mm 61.142 in
Width	1697 mm 66.811 in
Depth	395 mm 15.551 in
Enclosure Size	Large

Material Specifications

Finish	Powder coated polyester
Material Type	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space	Above ground
Qualification Standards	IEC 60529, IP55 IK10

Packaging and Weights

Included	Base with covers Blank cable inlet plate Mounting profiles for shelves
Packaging quantity	2
Packaging Type	Pallet
Note	Two cabinets supplied per Euro pallet, bolted and shrink wrapped in polythene with cardboard hosing protection strapped together for secure shipping