CC0561-000 | OCC1A-1200-S1ASENB

OCC1A Wideband Splitter, singlemode, 1x2, 50/50 ratio, SC/UPC, 0.9 mm cable, medium duty housing

Product Classification

Regional Availability	North America
Product Type	Splitter component
Product Series	OCC1A

General Specifications

Device Type	Component, tubular
Functionality	Splitting
Technology Type	Fused biconic tapered
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	1 x 2 splitter
Interface, Input	SC/UPC
Interface, Output	SC/UPC
Split Ratio	Symmetrical
Splitter, quantity	1
-	

Dimensions

Pigtail Length, Input	1.5 m 4.921 ft
Pigtail Length, Output	1.5 m 4.921 ft
Pigtail Diameter, Input	0.9 mm 0.035 in
Pigtail Diameter, Output	0.9 mm 0.035 in

Packaging and Weights

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023



CC0561-000 | OCC1A-1200-S1ASENB

Packaging quantity

Regulatory Compliance/Certifications

Agency

Classification

1

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS



Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

