



DLX to DLX Adapter

- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	DLX®
Product Series	FHD
Minimum Order Quantity	10

General Specifications

Body Style	Straight orientation
Color	Black
Interface	DLX
Shuttered	No
Total Ports, quantity	2

Optical Specifications

Insertion Loss, maximum	0.5 dB
Insertion Loss, maximum note	0.5 dB mated included DLX connectors
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Flammability Rating	UL 94 V-1
Qualification Standards	Telcordia GR-326-CORE
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity 10
Packaging Type Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

