

F1-PNMMU-3

FSJ1-50A Jumper with interface types N Male and MINI UHF MALE, 3 FT



Product Classification

Product Type	SureFlex® standard
Product Series	FSJ1-50A

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	Mini UHF Male
Specification Sheet Revision Level	A

Dimensions

Length	0.914 m 2.999 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
10–400 MHz	1.29	18

Jumper Assembly Sample Label

F1-PNMMU-3



Included Products

- F1MU – Mini UHF Male for 1/4 in FSJ1-50A cable
- F1TNM-LS – Type N Male for 1/4 in foam and air coaxial cable, factory attached
- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket