

760249050 | G2iP-SP-24LCG-PT

G2 Splice Cassette, 24LC/UPC intelligent-ready, without shutters, OS2, with pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Series	G2

General Specifications

Color, front	Blue
Intelligence Type	iPatch® ready
Interface, front	LC/UPC
Interface Feature, front	Dust caps
Interface, rear	Stranded pigtail
Shuttered	No
Total Fibers, quantity	24

Dimensions

Height	26.416 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	165.354 mm 6.51 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.2 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included	SMOUV holder SMOUV splice protection
-----------------	--

Packaging quantity 1
Weight, net 0.147 kg | 0.324 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

