## 760249310 | CPPA-IP-6A-STP-1U-24



#### CommScope® imVision® STP Cat 6A Modular Angled Panel, 24 port

#### **Product Classification**

 Regional Availability
 Asia | EMEA

 Portfolio
 CommScope®

 Product Type
 RJ45 patch panel

Product Brand imVision®

General Specifications

ANSI/TIA Category 6A

Cable TypeShieldedColorSilver

Intelligence Type iPatch® enabled

Panel Style Angled

Rack Units 1

Total Ports, quantity 24

**Wiring** T568A | T568B

**Dimensions** 

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 206.5 mm | 8.13 in

 Compatible Diameter Over Dielectric, maximum
 1.168 mm | 0.046 in

**Electrical Specifications** 

Current Rating at Temperature  $1.5 \text{ A} \otimes 20 \text{ °C} + 1.5 \text{ A} \otimes 68 \text{ °F}$ 

**Dielectric Withstand Voltage, RMS, conductive surface** 1,500 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm



# 760249310 | CPPA-IP-6A-STP-1U-24

### Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

**Environmental Specifications** 

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

