



CommScope® imVision® STP Cat 6A Modular Angled Panel, 24 port

Product Classification

Regional Availability	Asia EMEA
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Brand	imVision®

General Specifications

ANSI/TIA Category	6A
Cable Type	Shielded
Color	Silver
Intelligence Type	iPatch® enabled
Panel Style	Angled
Rack Units	1
Total Ports, quantity	24
Wiring	T568A T568B

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	206.5 mm 8.13 in
Compatible Diameter Over Dielectric, maximum	1.168 mm 0.046 in

Electrical Specifications

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

760249310 | CPPA-IP-6A-STP-1U-24

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

