

T-2-UW-NF



Termination Load, 0–6000 MHz

OBSOLETE

This product was discontinued on: September 30, 2021

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load

General Specifications

Device Type	Termination Load
Application	Indoor/Outdoor
Color	Black
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal

Dimensions


Length	40 mm 1.575 in
Diameter, maximum	20 mm 0.787 in

Electrical Specifications

Average Power at Temperature	1.7 W @ 60 °C
Average Power, maximum	2 W
Impedance	50 ohm
Operating Frequency Band	0 – 6000 MHz
VSWR	1.15

Derating Curve

T-2-UW-NF



Environmental Specifications

Operating Temperature	-35 °C to +50 °C (-31 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	68 mm 2.677 in
Width, packed	53 mm 2.087 in
Length, packed	580 mm 22.835 in
Weight, gross	0.06 kg 0.132 lb
Weight, net	0.04 kg 0.088 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

