

T-25-UW-NM



Termination Load, 0–6000 MHz

OBSOLETE

This product was discontinued on: **November 15, 2022**

Replaced By:

T-25-UW-43-M

Termination Load, 0–6000 MHz

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load

General Specifications

Device Type	Termination Load
Application	Indoor/Outdoor
Color	Black
Inner Contact Plating	Silver
Interface	N Male
Outer Contact Plating	Trimetal

Dimensions

Length	81 mm 3.189 in
Diameter, maximum	35 mm 1.378 in

Electrical Specifications

Average Power, maximum	25 W
Impedance	50 ohm
Operating Frequency Band	0 – 6000 MHz
VSWR	1.15

T-25-UW-NM

Environmental Specifications

Operating Temperature	-35 °C to +50 °C (-31 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	98 mm 3.858 in
Width, packed	53 mm 2.087 in
Length, packed	58 mm 2.283 in
Weight, gross	0.2 kg 0.441 lb
Weight, net	0.18 kg 0.397 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

