



MiniPod, category 6, 3 port, unloaded with angled adapters, unshielded

- Improved speed of redeployment in the workplace through rapid mechanism
- Simplified cabling of raised floor spaces and ideal for high density environments
- Ideal to be terminated at an early stage in the building works
- Designed for use with all standard flexible conduit systems

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Modular jack enclosure
Product Series	MiniPod

General Specifications

ANSI/TIA Category	6
Application	Used with KJ Series outlets
Cable Entry Location	Side
Color	Black
Conduit Fitting Size	25.1 mm 0.988 in
Integrated Dust Cover Type	Sliding
Mounting	Surface
Outlet Orientation	Flat
Total Ports, quantity	3

Dimensions

Height	47 mm 1.85 in
Width	185 mm 7.283 in
Depth	50 mm 1.969 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS)
----------------------	---------------------------------------

Environmental Specifications

2153216-3

Environmental Space Indoor
Flammability Rating UL 94 V-0

Packaging and Weights

Included Angled Keystone Adaptor (3) | Clear Label Window (3) | Label Insert (3) | MiniPod Subassembly (1) | Mounting screw (1)

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

