


760205625 | M81-270 BLANK

Blank Coaxial Adapter, Gray



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Adapter kit

General Specifications

Color	Gray
Mounting	Snap-in

Dimensions

Height	17.53 mm 0.69 in
Width	24.38 mm 0.96 in
Depth	12.95 mm 0.51 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing
Flammability Rating	UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

760205625 | M81-270 BLANK

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

