## 760238472 | FMK600-P.WH



### SL-Series FMK Modular Jack, RJ45, Cat6, Unshielded, ProWhite

#### **Product Classification**

Regional Availability

Australia/New Zealand

Portfolio NETCONNECT®

**Product Type** Modular jack

**Product Series** SL Series

General Specifications

ANSI/TIA Category 6

Cable Type Unshielded

**Color** Pro white

Conductor Type Solid | Stranded

Integrated Dust Cover Type None

**Mounting** Clipsal/HPM faceplates

Outlet Feature Inverted jack face

Outlet Type Standard

**Termination Tool** SL Termination tool

Termination Type IDC

**Transmission Standards**ANSI/TIA-568-C.2 | ISO/IEC 11801 Class E

**Wiring** T568A | T568B

Dimensions

Panel Thickness, recommended 1.6 mm | 0.063 in Compatible Insulated Conductor Diameter, maximum 1.45 mm | 0.057 in

Contact Plating Thickness1.27 μmCompatible Conductor Gauge, solid24-22 AWGCompatible Conductor Gauge, stranded26-24 AWG

**Electrical Specifications** 

**COMMSCOPE®** 

# 760238472 | FMK600-P.WH

**Remote Powering** Fully supports the safe delivery of power over LAN cabling described

by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

PoE Durability Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000

plug to jack mating cycles

Material Specifications

Contact Base Material Beryllium copper

Contact Plating Material Gold

Material Type Polycarbonate

Mechanical Specifications

Plug to Jack Mating Cycles Complies to IEC 60603-7 series

**Environmental Specifications** 

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 10
Packaging Type Bag

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



