

# 760242344 | SFC-LCF-UNV-8X QWIK II™ LC



Qwik II® Field Installable LC Connector, Singlemode-UPC, Blue, for 0.25 /0.9/2.0/3.0 mm, single pack

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	Qwik II®   TeraSPEED®
Product Series	Qwik II

## General Specifications

Body Style	Universal
Color, boot	Black
Color, housing	Blue
Ferrule Geometry	Factory polished
Interface	LC/UPC
Interface Feature	Field Installable   Mechanical splice

## Dimensions

Compatible Cable Diameter	0.25 mm   0.01 in   0.9 mm   0.035 in   2 mm   0.079 in   3 mm   0.118 in
---------------------------	---

## Material Specifications

Ferrule Material	Zirconia
------------------	----------

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.5 dB
Insertion Loss, typical	0.2 dB

# 760242344 | SFC-LCF-UNV-8X QWIK II™ LC

**Return Loss, minimum** 45 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

