



Qwik II® Field Installable SC Connector, OM3/4/5, Aqua, for 0.25/0.9/2.0 /3.0 mm, single pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	LazrSPEED® Qwik II®
Product Series	Qwik II

General Specifications

Body Style	Universal
Color, boot	Black
Color, housing	Aqua
Ferrule Geometry	Factory polished
Interface	SC/UPC
Interface Feature	Field Installable Mechanical splice

Dimensions

Compatible Cable Diameter	0.25 mm 0.01 in 0.9 mm 0.035 in 2 mm 0.079 in 3 mm 0.118 in
---------------------------	---

Material Specifications

Ferrule Material	Zirconia
------------------	----------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM3 OM4 OM5, LazrSPEED® wideband
Insertion Loss, maximum	0.5 dB
Insertion Loss, typical	0.1 dB
Return Loss, minimum	20 dB

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

