

# 760242346 | MFC-SCF-UNV-5X QWIK II™ SC



Qwik II® Field Installable SC Connector, OM3/4/5, Aqua, for 0.25/0.9/2.0 /3.0 mm, single pack

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber connector
<b>Product Brand</b>	LazrSPEED®   Qwik II®
<b>Product Series</b>	Qwik II

## General Specifications

<b>Body Style</b>	Universal
<b>Color, boot</b>	Black
<b>Color, housing</b>	Aqua
<b>Ferrule Geometry</b>	Factory polished
<b>Interface</b>	SC/UPC
<b>Interface Feature</b>	Field Installable   Mechanical splice

## Dimensions

<b>Compatible Cable Diameter</b>	0.25 mm   0.01 in   0.9 mm   0.035 in   2 mm   0.079 in   3 mm   0.118 in
----------------------------------	---------------------------------------------------------------------------

## Material Specifications

<b>Ferrule Material</b>	Zirconia
-------------------------	----------

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM3   OM4   OM5, LazrSPEED® wideband
<b>Insertion Loss, maximum</b>	0.5 dB
<b>Insertion Loss, typical</b>	0.1 dB
<b>Return Loss, minimum</b>	20 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

