760243388 | SFC-LCF-20-8Y-12-PACK

Qwik-Fuse Connector, LC, Singlemode-UPC, Blue, for 1.6/2.0 mm, 12 per pack

OBSOLETE
Replaced By:

760258744	Qwik-Fuse Connector, LC, Singlemode-UPC, Blue, for 1.6/2.0 mm, 12 per pack

Product Classification

Regional Availability	Asia	Australia/New Zealand	EMEA	Latin America	North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	Qwik	TeraSPEED®
Product Series	Qwik-Fuse

General Specifications

Body Style	Cordage
Color, boot	Blue
Color, housing	Blue
Ferrule Geometry	Factory polished
Interface	LC/UPC
Interface Feature	Field Installable	Fusion splice

Dimensions

Compatible Cable Diameter	1.6 mm	0.063 in	2 mm	0.079 in

Material Specifications

Ferrule Material	Zirconia

Mechanical Specifications

Cable Retention Strength, maximum	5.08 lb @ 0 °

COMMSCOPE®

760243388 | SFC-LCF-20-8Y-12-PACK

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Optical Components Standard	ANSI/TIA-568. 3-D	GR-1081	IEC 61753-1
Insertion Loss, maximum	0.3 dB
Insertion Loss, typical	0.15 dB
Return Loss, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity	12

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

COMMSCOPE®