



LF80 U/F/STP-262 Shuttered Faceplate Module, White, 1 Port, Antimicrobial treated

- The product contains an antimicrobial additive based on a silver ions powder in a PC (Polycarbonate) carrier, it meet the ISO 22196 Test for Antimicrobial Activity of Plastics
- Compatible with F/UTP & U/UTP applications

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Module
Product Series	M Series

General Specifications

Application	Used with M Series modular information outlet
Color	White
Mounting	Flush
Outlet Type	M Series
Total Ports, quantity	1

Dimensions

Height	38.354 mm 1.51 in
Width	24.638 mm 0.97 in
Depth	14.732 mm 0.58 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing

760245047 | LF80-WHITE

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Weight, net 0.005 kg | 0.01 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

