CK9100-000 | HFTP-N0-S111-E



HFTP Customer premises fiber wall outlet, SC/UPC, one pigtail, one adapter

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Can be wall mounted and mounted on wall boxes with fixation points of 60mm
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

Product Classification

Regional Availability EMEA
Product Type Outlet
Product Series HFTP
Minimum Order Quantity 300

General Specifications

ColorWhiteCover TypeScrew-onInterface TypeSC/UPCMountingWall mount

Total Ports, quantity 1

Dimensions

 Height
 105.41 mm | 4.15 in


 Width
 82.55 mm | 3.25 in


 Depth
 23.876 mm | 0.94 in

Outline Drawing



CK9100-000 | HFTP-N0-S111-E





Material Specifications

Material Type LSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Storage Temperature $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Relative Humidity Up to 93%, non-condensing

Environmental Space Indoor

Packaging and Weights

Packaging quantity 10

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

COMMSCOPE®

CK9100-000 | HFTP-NO-S111-E



Included Products

CK7246-000 HFTP-N0-NN00-E HFTP Customer premises fiber wall outlet, no adapters, no pigtails, for splicing only

Page 3 of 3