

1375055-3



SL110 Series Modular Jack, RJ45, category 6, T568A/T568B, unshielded, without dust cover, white

OBSOLETE

This product was discontinued on: June 13, 2018

Replaced By:

1-1375055-3
SL110-6-P.WH

SL-Series Modular Jack, RJ45, Cat6 Unshielded, ProWhite

Product Classification

| | |
|-----------------------|--------------------------------------|
| Regional Availability | Asia Latin America North America |
| Portfolio | NETCONNECT® |
| Product Type | Modular jack |
| Product Series | SL Series |

General Specifications

| | |
|---------------------------------|---------------------------------|
| ANSI/TIA Category | 6 |
| Cable Type | Unshielded |
| Color | White |
| Conductor Type | Solid Stranded |
| Integrated Dust Cover Type | None |
| Mounting | SL Series faceplates and panels |
| Outlet Feature | Inverted jack face |
| Outlet Type | Standard |
| Termination Punchdowns, minimum | 200 times |
| Termination Tool | SL Termination tool |
| Termination Type | IDC |

1375055-3

| | |
|--|--|
| Transmission Standards | ANSI/TIA-568-C.2 ISO/IEC 11801 Class E |
| Wiring | T568A T568B |
| Dimensions | |
| Panel Cutout, recommended | 14.78 x 20.07 mm (0.58 x 0.79 in) |
| Panel Thickness, recommended | 1.6 mm 0.063 in |
| Height | 16.26 mm 0.64 in |
| Width | 14.48 mm 0.57 in |
| Depth | 30.48 mm 1.2 in |
| Compatible Insulated Conductor Diameter, maximum | 1.45 mm 0.057 in |
| Contact Plating Thickness | 1.27 µm |
| Compatible Conductor Gauge, solid | 24–22 AWG |
| Compatible Conductor Gauge, stranded | 26–24 AWG |
| Electrical Specifications | |
| PoE Durability | Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles |
| Safety Voltage Rating | 150 Vac |
| Material Specifications | |
| Contact Base Material | Beryllium copper |
| Contact Plating Material | Gold |
| Material Type | Polycarbonate |
| Mechanical Specifications | |
| Plug Retention Force, minimum | 89 N 20.008 lbf |
| Plug to Jack Mating Cycles | Complies to IEC 60603-7 series |
| Environmental Specifications | |
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | CSA cUL |
| Packaging and Weights | |
| Included | Strain relief cap |

| | |
|--------------------|-----|
| Packaging quantity | 1 |
| Packaging Type | Bag |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

