



JACK, AMP-TWIST, UTP, C6A, WHITE

**OBSOLETE**

This product was discontinued on: June 13, 2018

**Replaced By:**

1-1933476-3      JACK, AMP-TWIST, UTP, C6A, A. WHITE

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America
Portfolio	NETCONNECT®
Product Type	Modular jack
Product Series	SL Series

General Specifications

ANSI/TIA Category	6A
Cable Type	Unshielded
Color	White
Conductor Type	Solid   Stranded
Integrated Dust Cover Type	None
Mounting	SL Series faceplates and panels
Outlet Feature	Inverted jack face
Outlet Type	Standard
Termination Tool	SL Termination tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2   ISO/IEC 11801 Class EA
Wiring	T568A   T568B

Dimensions

Panel Cutout, recommended	14.78 x 20.32 mm (0.58 x 0.80 in)
Panel Thickness, recommended	1.6 mm   0.063 in
Height	21.5 mm   0.846 in
Width	15.25 mm   0.6 in
Depth	39.03 mm   1.537 in
Compatible Cable Diameter, maximum	9 mm   0.354 in
Compatible Insulated Conductor Diameter, maximum	1.6 mm   0.063 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	24–22 AWG
Compatible Conductor Gauge, stranded	24 AWG

Electrical Specifications

Safety Voltage Rating	150 Vac
-----------------------	---------

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	750 times
------------------------------	-----------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	cUL

Packaging and Weights

Included	Strain relief cap
Packaging quantity	24

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# 1933476-3

---

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

