

FGS-HNTS-14MM



FiberGuide® Top Support C-Bracket Kit, 14mm for 2x6, 4x4, 4x6in Systems

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS
Minimum Order Quantity	10

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Bracket
Bracket Type	C-bracket
Bracket Installation Type	No Brackets
Attachment Type	Threaded rod

Dimensions

Height	304.8 mm 12 in
Width	38.1 mm 1.5 in
Length	203.2 mm 8 in
Thread Size	14 mm
System Dimensions	102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 51 mm x 152 mm (2 in x 6 in)

Ordering Tree

FGS-HNTS-14MM

FGS - HNTS - ⁹F - ¹⁰5/8 - ¹¹A

For Section Size

9	empty	4 x 4 in, 4 x 6 in
	F	4 x 12 in

For Threaded Rod Size

10	1/2	1/2 in
	1/2-LP	1/2 in, low profile
	12MM	12 mm
	12MM-LP	12 mm, low profile
	14MM	14 mm
	14MM-LP	14 mm, low profile
	16MM	16 mm
	16MM-LP	16 mm, low profile
	5/8	5/8 in
	5/8-LP	5/8 in, low profile

11	A	Adjustable
----	---	------------

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware | Locking Washers | Nuts | Quick Knobs | Screws | Washers

Packaging quantity 1

Weight, net 1.004 kg | 2.213 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

