

FGS-HNTS-F-12MM



FiberGuide® Top Support C-Bracket Kit, 12mm for 4x12in System

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Support mounting kit |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|----------------------------------|--------------|
| Color | Black |
| Orientation | Horizontal |
| Section Type | Bracket |
| Bracket Type | C-bracket |
| Bracket Installation Type | No Brackets |
| Attachment Type | Threaded rod |

Dimensions

| | |
|--------------------------|--------------------------------|
| Height | 304.8 mm 12 in |
| Width | 38.1 mm 1.5 in |
| Length | 381 mm 15 in |
| Thread Size | 12 mm |
| System Dimensions | 102 mm x 305 mm (4 in x 12 in) |

Ordering Tree

FGS-HNTS-F-12MM

FGS - - - - - - -

For Section Size

| | | |
|---|------------------------------------|--------------------|
| 9 | <input type="text" value="empty"/> | 4 x 4 in, 4 x 6 in |
| | <input type="text" value="F"/> | 4 x 12 in |

For Threaded Rod Size

| | | |
|----|--------------------------------------|---------------------|
| 10 | <input type="text" value="1/2"/> | 1/2 in |
| | <input type="text" value="1/2-LP"/> | 1/2 in, low profile |
| | <input type="text" value="12MM"/> | 12 mm |
| | <input type="text" value="12MM-LP"/> | 12 mm, low profile |
| | <input type="text" value="14MM"/> | 14 mm |
| | <input type="text" value="14MM-LP"/> | 14 mm, low profile |
| | <input type="text" value="16MM"/> | 16 mm |
| | <input type="text" value="16MM-LP"/> | 16 mm, low profile |
| | <input type="text" value="5/8"/> | 5/8 in |
| | <input type="text" value="5/8-LP"/> | 5/8 in, low profile |

| | | |
|----|--------------------------------|------------|
| 11 | <input type="text" value="A"/> | Adjustable |
|----|--------------------------------|------------|

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware

Packaging quantity 1

Weight, net 1.41 kg | 3.109 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

