

FGS-HNTS-F-16MM



FiberGuide® Top Support C-Bracket Kit, 16mm for 4x12in System

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Bracket
Bracket Type	C-bracket
Bracket Installation Type	N/A
Attachment Type	Threaded rod

Dimensions

Height	304.8 mm 12 in
Width	50.8 mm 2 in
Length	381 mm 15 in
Thread Size	16 mm
System Dimensions	102 mm x 305 mm (4 in x 12 in)

Ordering Tree

FGS-HNTS-F-16MM

FGS -

HNTS

 -

9

F

 -

10

5/8

 -

11

A

For Section Size

9

empty

4 x 4 in, 4 x 6 in

F

4 x 12 in

For Threaded Rod Size

10

1/2

1/2 in

1/2-LP

1/2 in, low profile

12MM

12 mm

12MM-LP

12 mm, low profile

14MM

14 mm

14MM-LP

14 mm, low profile

16MM

16 mm

16MM-LP

16 mm, low profile

5/8

5/8 in

5/8-LP

5/8 in, low profile

11

A

Adjustable

Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware

Packaging quantity 1

Weight, net 1.765 kg | 3.89 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

