

# FGS-HTUB-14MM

---



FiberGuide® Center Support Bracket Kit, 14mm for 2x6, 4x4, 4x6in Systems

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Support mounting kit  |
| <b>Product Brand</b>         | FiberGuide®   |
| <b>Product Series</b>        | FGS   |

## General Specifications

|                                  |                |
|----------------------------------|----------------|
| <b>Color</b>                     | Black          |
| <b>Orientation</b>               | Horizontal     |
| <b>Section Type</b>              | Bracket        |
| <b>Bracket Type</b>              | Center Support |
| <b>Bracket Installation Type</b> | No Brackets    |
| <b>Attachment Type</b>           | Threaded rod   |

## Dimensions

|                          |  |
|--------------------------|--|
| <b>Width</b>             | 63 mm   2.48 in  |
| <b>Thread Size</b>       | 14 mm  |
| <b>System Dimensions</b> | 102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   51 mm x 152 mm (2 in x 6 in) |

## Ordering Tree

# FGS-HTUB-14MM



### For Section Size

|   |       |                    |
|---|-------|--------------------|
| 9 | empty | 4 x 4 in, 4 x 6 in |
|   | F     | 4 x 12 in          |

### For Threaded Rod Size

|    |      |        |
|----|------|--------|
| 10 | 1/2  | 1/2 in |
|    | 10MM | 10 mm  |
|    | 12MM | 12 mm  |
|    | 14MM | 14 mm  |
|    | 16MM | 16 mm  |
|    | 5/8  | 5/8 in |

## Packaging and Weights

**Weight, net** 0.4 kg | 0.882 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS  
REACH-SVHC  
ROHS  
UK-ROHS

### Classification

Below maximum concentration value  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant  
Compliant

