FGS-KT03-C-15F



FiberGuide® Dual 7/8in Flex Tube Attachment, 2x2in, 15ft Length, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeConvoluted tube

Product Brand FiberGuide®

Product Series FGS

General Specifications

ColorYellowOrientationVerticalSection TypeAdapter

Dimensions

 Height
 127 mm | 5 in

 Width
 381 mm | 15 in

 Length
 508 mm | 20 in

Tube Outer Diameter 22.35 mm | 0.88 in

System Dimensions 51 mm x 51 mm (2 in x 2 in)

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.423 kg | 0.933 lb

Regulatory Compliance/Certifications

COMMSCOPE®

FGS-KT03-C-15F

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

