FGS-MH4E-A



FiberGuide® 45° Horizontal Elbow, 4x4in, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Elbow
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Angle/Bend Direction	45°
Color	Yellow
Orientation	Horizontal
Section Type	Elbow section
Dimensions	
Height	112 mm 4.409 in
Width	347 mm 13.661 in
Length	398 mm 15.669 in
System Dimensions	102 mm x 102 mm (4 in x 4 in)

Ordering Tree

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 21, 2025



FGS-MH4E-A



yellow

black

Section Color

9

Section Size

10

А	4 x 4 in
В	4 x 6 in
F	4 x 12 in
G	2 x 6 in
Н	4 x 24 in
H-VS	4 x 24 in, variable support bracket

* Support brackets only come in black

Material Specifications

Material Type

Engineering Thermoplastic

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Weight, net 0.69 kg | 1.521 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 21, 2025

