FGS-MH4E-G



FiberGuide® 45° Horizontal Elbow, 2x6in, Yellow

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Elbow

Product Brand FiberGuide®

Product Series FGS

General Specifications

Angle/Bend Direction 45°

Color Yellow


Orientation Horizontal

Section Type Elbow section

Dimensions

System Dimensions 51 mm x 152 mm (2 in x 6 in)

Ordering Tree



Section Color

9	empty	yellow	
9	В	black	

* Support brackets only come in black

Section Size

10	Α	4 x 4 in
	В	4 x 6 in
	F	4 x 12 in
	G	2 x 6 in
	Н	4 x 24 in
Ì	H-VS	4 x 24 in, variable support bracket

Page 1 of 2



FGS-MH4E-G

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.01 kg | 0.022 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

