

FGS-MU4E-B



FiberGuide® 45° Up Elbow, 4x6in, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Elbow
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Angle/Bend Direction	45° up
Color	Yellow
Orientation	Horizontal
Section Type	Elbow section

Dimensions

Height	166 mm 6.535 in
Width	213 mm 8.386 in
System Dimensions	102 mm x 152 mm (4 in x 6 in)

Ordering Tree

FGS-MU4E-B



Section Color

9	empty	yellow
	B	black

Section Size

10	A	4 x 4 in
	B	4 x 6 in
	C	2 x 2 in*
	F	4 x 12 in
	G	2 x 6 in
	H	4 x 24 in

* FGS-MU4A-C or FGSB-MU4A-C

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.8 kg | 1.764 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

