

# FGSB-MFTY-500F

---



FiberGuide® 7/8in Flex Tube, Slotted, 500ft Length, Black

## OBSOLETE

This product was discontinued on: October 1, 2023

### Replaced By:

FGSB-MFTY-250F      FiberGuide® 7/8in Flex Tube, Slotted, 250ft Length, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Convolute tube
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications


<b>Product Feature</b>	Round
<b>Color</b>	Black
<b>Orientation</b>	Vertical
<b>Section Type</b>	Vertical section

## Dimensions

<b>Length</b>	152400 mm   6,000.003 in
<b>Tube Outer Diameter</b>	567.69 mm   22.35 in

## Ordering Tree

# FGSB-MFTY-500F



## Tube Color

9	empty	yellow
	B	black

## Tube Length, examples

11	5F	5 feet
	350F	350 feet

## Tube Type

10	MIDY	Slotted flexible tube, 2 in diameter
	MFTY	Slotted flexible tube, 7/8 in diameter
	MISY	Solid flexible tube, 2 in diameter
	MLDY	Slotted flexible tube, 1 in diameter

## Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

## Packaging and Weights

**Weight, net** 5.125 kg | 11.299 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

