FGSB-MSHS-B-RW



FiberGuide® Horizontal Straight Section with Pre-Cut 6in Spacing and 2.25in Opening, 4x6 in, Black

Product Classification

Asia Australia/New Zealand EMEA Latin America North America
CommScope®
Straight section
FiberGuide®
FGS

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Straight section

Dimensions

Height	101.6 mm 4 in
Width	152.4 mm 6 in
Length	1829 mm 72.008 in
System Dimensions	102 mm x 152 mm (4 in x 6 in)

Material Specifications

Material TypeEngineering Thermoplastic

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

 Weight, net
 3.507 kg | 7.732 lb

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 28, 2025



(e

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 28, 2025

