# LS2-XMHM-3M-P



LSF2-50 SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male, 3m

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

#### **Product Classification**

**Product Type** Wireless transmission cable assembly

Product Series LSF2-50

## General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector ANEX10 MaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level A

#### Dimensions

**Length** 3 m | 9.843 ft

Nominal Size 3/8 in

### **Electrical Specifications**

**3rd Order IMD** -116 dBm

**3rd Order IMD Test Method** Two +43 dBm carriers

#### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30.04
1700-2200 MHz	1.083	27.99
2500-2700 MHz	1.106	25.96
3400-3800 MHz	1.222	20.01



# LS2-XMHM-3M-P

### Jumper Assembly Sample Label



#### **Environmental Specifications**

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

#### Included Products

LS2XM-P – NEX10 Male for 3/8 in LSF2-50 cable, factory attached

LSF2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket

(Not for Individual Sale - Jumpers only)

P4HM-S2 - 4.3-10 Male for 3/8 in LSF2-50 cable, factory attached

