

# SVAPA12V200C

---



HomeConnect® Power Adapter for Subscriber Amplifiers, ac/dc, 12 V, 200 mA

**OBSOLETE**

## Product Classification

<b>Product Type</b>	RF amplifier power adapter
<b>Product Brand</b>	HomeConnect®

## General Specifications

<b>Plug Type</b>	Type C
------------------	--------

## Electrical Specifications

<b>Input Current, maximum</b>	35 mA
<b>Input Voltage @ Voltage at Frequency</b>	230 Vac @ 50 Hz
<b>Output Voltage Tolerance, no load</b>	±5%
<b>Output Voltage, no load</b>	17.5 Vdc
<b>Operating Current at Voltage</b>	300 mA @ 12 Vdc

## Environmental Specifications

<b>Safety Standard</b>	CE
------------------------	----

## Packaging and Weights

<b>Height, packed</b>	279.4 mm   11 in
<b>Width, packed</b>	304.8 mm   12 in
<b>Length, packed</b>	381 mm   15 in
<b>Carton Quantity</b>	60

# SVAPA12V200C

---

**Weight, gross**

19.051 kg | 42 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

