

SVLTA



HomeConnect® Locking Terminator, brass

OBSOLETE

Product Classification

Product Type	Terminator
Product Brand	HomeConnect®

General Specifications

Device Type	Locking terminator
Parking Port	Included

Dimensions

Contact Pin Diameter	0.813 mm 0.032 in
Contact Pin Diameter Tolerance	±0.002 in

Electrical Specifications

Return Loss at Frequency Band, minimum	20 dB @ 1700–2000 MHz 24 dB @ 1002–1700 MHz 25 dB @ 1002–1500 MHz 30 dB @ 5–1002 MHz
Impedance	75 ohm
Operating Frequency Band	5 – 2000 MHz

Material Specifications

Material Type	Brass
Plating	Nickel

Environmental Specifications

SVLTA

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	CE EN 60728-4 SCTE

Packaging and Weights

Height, packed	190.5 mm 7.5 in
Width, packed	241.3 mm 9.5 in
Length, packed	330.2 mm 13 in
Carton Quantity	1250
Weight, gross	19.051 kg 42 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

