

# SVLT

---

HomeConnect® Locking Terminator, brass, ac/dc block



**OBSOLETE**

## Product Classification

|                      |              |
|----------------------|--------------|
| <b>Product Type</b>  | Terminator   |
| <b>Product Brand</b> | HomeConnect® |

## General Specifications

|                     |                    |
|---------------------|--------------------|
| <b>Device Type</b>  | Locking terminator |
| <b>Parking Port</b> | Included           |

## Dimensions

|                                       |                     |
|---------------------------------------|---------------------|
| <b>Contact Pin Diameter</b>           | 0.813 mm   0.032 in |
| <b>Contact Pin Diameter Tolerance</b> | ±0.002 in           |

## Electrical Specifications

|                                 |              |
|---------------------------------|--------------|
| <b>Return Loss, minimum</b>     | 30 dB        |
| <b>Impedance</b>                | 75 ohm       |
| <b>Operating Frequency Band</b> | 5 – 1800 MHz |

## Material Specifications

|                      |        |
|----------------------|--------|
| <b>Material Type</b> | Brass  |
| <b>Plating</b>       | Nickel |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -40 °C to +60 °C (-40 °F to +140 °F) |
|------------------------------|--------------------------------------|

# SVLT

---

**Safety Standard** CE | EN 60728-4 | SCTE

## Packaging and Weights

**Height, packed** 190.5 mm | 7.5 in

**Width, packed** 241.3 mm | 9.5 in

**Length, packed** 330.2 mm | 13 in

**Carton Quantity** 1000

**Weight, gross** 19.051 kg | 42 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

