

# D35163-000 | OCC1A-1200-L2ASENB

---

OCC1A Wideband Splitter, singlemode, 1x2, 50/50 ratio, LC/APC, 0.9 mm cable, medium duty housing



## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Splitter component
<b>Product Series</b>	OCC1A

## General Specifications

<b>Device Type</b>	Component, tubular
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Fused biconic tapered
<b>Application</b>	For use in FOOSC closures
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 2 splitter
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Pigtail Length, Input</b>	1.5 m   4.921 ft
<b>Pigtail Length, Output</b>	1.5 m   4.921 ft
<b>Pigtail Diameter, Input</b>	0.9 mm   0.035 in
<b>Pigtail Diameter, Output</b>	0.9 mm   0.035 in

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

