



RPBS wraparound delivery sleeve heat shrink kit, pressurized, for 50 to 70 mm cable diameter, 200 mm inner sheet opening, 500 mm outer sheet opening

- Combines an improved application method for standard resin blocking compounds with the advantages of the wraparound heat-shrinkable sleeve
- Used with suitable commercially available resins, the system forms a pressure block for the whole pressurized cable range

OBSOLETE

This product was discontinued on: May 2, 2023

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink delivery sleeve
Product Series	RPBS

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Height	325 mm 12.795 in
Length	700 mm 27.559 in
Expanded Inside Diameter, minimum	70 mm 2.756 in
Recovered Inside Diameter, maximum	50 mm 1.969 in
Single Cable Diameter, maximum	70 mm 2.756 in
Single Cable Diameter, minimum	50 mm 1.969 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

Environmental Specifications

188606-000 | RPBS-C-II-70/50-200

Environmental Space Buried | Ducted

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

