

Boot Assembly, 4 in

Product Classification

Product Type Boot assembly

Product Brand I-Line

Ordering Note ANDREW® non-standard product

General Specifications

Cable Type Corrugated

Color Black

Dimensions

 Height
 101.6 mm | 4 in

 Length
 76.2 mm | 3 in

Material Specifications

Material Type EPDM rubber

Environmental Specifications

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packaging and Weights

 Height, packed
 170.18 mm | 6.7 in

 Width, packed
 129.54 mm | 5.1 in

 Length, packed
 99.06 mm | 3.9 in

 Included
 Boot | Two clamps

Packaging quantity 1

Weight, gross 0.8 kg | 1.764 lb

ANDREW® an Amphenol company

294573

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

