



4 in boot cushion insert with 4 holes for 7/8 in corrugated coaxial cable

Product Classification

| | |
|----------------------|---------------------------------|
| Product Type | Cushion insert |
| Product Brand | I-Line |
| Ordering Note | CommScope® non-standard product |

General Specifications

| | |
|---------------------------|------------|
| Cable Type | Corrugated |
| Cables per Cushion | 4 |
| Color | Black |

Dimensions

| | |
|---------------------|--------------------|
| Height | 82.55 mm 3.25 in |
| Length | 25.4 mm 1 in |
| Nominal Size | 7/8 in |

Material Specifications

| | |
|----------------------|-------------|
| Material Type | EPDM rubber |
|----------------------|-------------|

Environmental Specifications

| | |
|---|--|
| UV Resistance Test Method | MIL-STD-810E, Procedure 11, Method 505 |
| UV Resistance, minimum with no degradation | ≥1000 hours |
| Weather Resistance Test Method | 04AS00-03.9.0 IEC 60529:2001, IP66 |

Packaging and Weights

| | |
|-----------------------|--------------------|
| Height, packed | 170.18 mm 6.7 in |
| Width, packed | 129.54 mm 5.1 in |
| Length, packed | 99.06 mm 3.9 in |
| Included | Cushion |

294700

Packaging quantity 1
Weight, gross 0.5 kg | 1.102 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |