338861-000 | FOSC-OC-6DBD1201NN

FOSC® A-TRAY-24 type, DWDM, 8 channels + upgrade port, demux, 1561.42 nm starting wavelength, 100 GHz channel spacing

Product Classification

Regional Availability North America

Product Type DWDM splice tray

Product Brand FOSC®
Product Series FOSC-OC

General Specifications

Application For use in FOSC closures

Interface, InputStub tailInterface, OutputStub tail

Dimensions

 Height
 9.2 mm | 0.362 in

 Depth
 10.67 mm | 0.42 in

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



338861-000 | FOSC-OC-6DBD1201NN



