

RPBS wraparound delivery sleeve heat shrink kit, pressurized, for 25 to 50 mm cable diameter, 150 mm sheet opening



- Combines an improved application method for standard resin blocking compounds with the advantages of the wraparound heat-shrinkable sleeve
- Used with suitable commercially available resins, the system forms a pressure block for the whole pressurized cable range

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Heat shrink delivery sleeve
<b>Product Series</b>	RPBS

## General Specifications

<b>Color</b>	Black
<b>Sealant Type</b>	Hotmelt adhesive

## Dimensions

<b>Height</b>	270 mm   10.63 in
<b>Length</b>	500 mm   19.685 in
<b>Expanded Inside Diameter, minimum</b>	50 mm   1.969 in
<b>Recovered Inside Diameter, maximum</b>	25 mm   0.984 in
<b>Single Cable Diameter, maximum</b>	50 mm   1.969 in
<b>Single Cable Diameter, minimum</b>	25 mm   0.984 in

## Material Specifications

<b>Material Type</b>	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

## Environmental Specifications

# 722356-000 | RPBS-C-I-50/25-150

---

## Environmental Space

Buried | Ducted

## Packaging and Weights

### Packaging quantity

1

### Packaging Type

Bag | Carton

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

