



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 50 mm/16 mm Shrink ratio, 1000 mm long, uncoated, 10 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

Product Classification

| | |
|------------------------------|---------------------------------|
| Regional Availability | EMEA |
| Product Type | Heat shrink tubing, medium wall |
| Product Series | MWTM |

General Specifications

| | |
|---------------------|----------|
| Color | Black |
| Sealant Type | Uncoated |

Dimensions

| | |
|-------------------------------------------|--------------------|
| Length | 1000 mm 39.37 in |
| Expanded Inside Diameter, minimum | 50 mm 1.969 in |
| Recovered Inside Diameter, maximum | 16 mm 0.63 in |
| Recovered Wall Thickness, minimum | 2 mm 0.079 in |

Material Specifications

| | |
|----------------------|------------|
| Material Type | Polyolefin |
|----------------------|------------|

Environmental Specifications

| | |
|----------------------------|-----------------|
| Environmental Space | Aerial Ducted |
|----------------------------|-----------------|

Packaging and Weights

| | |
|---------------------------|--------------|
| Packaging quantity | 10 |
| Packaging Type | Bag Carton |